



**Base:**  
**467-9**  
**100 parts**


**Curing Solution:**  
**CA-41B**  
**2.9 parts**




**At 75-80°F:**  
**(24-27°C)**

**Pot life:** **4 hours**  
**Induction Time:** **30 minutes**




**Dry film thickness:** **5 to 8 mils (127 - 203 microns)**



**At 75 to 80°F & 50% RH**


**Dry to Touch:** **2 Hours**  
**Dry to Sand:** **6 Hours**

**Clean Up:** **Use TR-36, MEK or applicable cleaning solvent**



**Dry to Touch:** **2 Hours**  
**Dry to Sand:** **6 Hours**

**Clean Up:** **Use TR-36, MEK or applicable cleaning solvent**



Type equipment	Tip Size	Gun Air Pres.	Pot Air Pres.	Other
Conventional spray gun	.052-.070 in	60-70 psi	5-20 psi	Low transfer efficiency
HVLP	1.2-1.4 mm	8-25 psi	Varies w/pot size	Iwata, Sata, Binks Mach 1
Low Pres. Electrostatic	1.2-1.5 mm	35-45 psi	12-100 psi	PRO3500, 4500SC
Air Assisted Electrostatic	.009-.013 in	65-75 psi	850-1000 psi	PRO4000AA, Ransburg (tips 1.2-1.5 mm)
Air Assisted Electrostatic	.009-.013 in	60-75 psi	1800-2500 psi	PRO4500AA

We have taken reasonable care in preparing the Mixing Guide and in collecting and preparing material for inclusion in it but do not represent or warrant that it is free from error or that the information content is complete or accurate. The information is advisory only and the use of the Material is solely at your own risk.